



Hexagon socket head cap screw DIN 912 Stainless steel A4 80 M12X55

Article number	53570.120.055
Brand	-
UBB	500571285500
UNSPSC	31161605
EAN	8715494136440
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	55 mm
Class	80
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

NEN	1241
DIN	912
BS	4168-1
NF	E25-125
ISO	4762
ASME	B18.3.1M

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	12
L (mm)	55
P	1.75
s	10

Technical Drawing

