

## Hexagon head bolt DIN 931 Stainless steel A4 70 M5X25

Article number	55000.050.025
Brand	-
UBB	500633329726
UNSPSC	31161620
EAN	8715494615761
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	25
Class	70
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

### Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

### Technical Specification

b (min.): 125mm<L≤200mm	22
b (min.): L≤125mm	16
k	3.5
P	0.80
s	8

### Technical Drawing

