

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M6X140

Article number	55000.060.140
Brand	-
UBB	951351769314
UNSPSC	31161620
EAN	8715492320162
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M6
Length	140 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	140
P	1
s	10

Technical Drawing

