

Hexagon head bolt DIN 931 Stainless steel A4 70 M8X55

Article number	55000.080.055
Brand	-
UBB	950351847385
UNSPSC	31161620
EAN	8715492320254
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	55 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	55
P	1.25
s	13

Technical Drawing

