

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M8X140

Article number	55000.080.140
Brand	-
UBB	950351848292
UNSPSC	31161620
EAN	8715492320360
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	140
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	28
b (min.): L≤125mm	22
k	5.3
P	1.25
s	13

Technical Drawing

