

## Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M8X160

Article number	55000.080.160
Brand	-
UBB	951351770205
UNSPSC	31161620
EAN	8715492320384
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	160
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info  
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

### Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

### Technical Specification

b (min.): 125mm<L≤200mm	28
b (min.): L≤125mm	22
k	5.3
P	1.25
s	13

### Technical Drawing

