

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M8X170

Article number	55000.080.170
Brand	-
UBB	951351770387
UNSPSC	31161620
EAN	8715492320391
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M8
Length	170 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	170
P	1.25
s	13

Technical Drawing

