

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M8X220

Article number	55000.080.220
Brand	-
UBB	952351691250
UNSPSC	31161620
EAN	8715492320438
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M8
Length	220 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	220
P	1.25
s	13

Technical Drawing

