

Hexagon head bolt DIN 931 Stainless steel A4 70 M10X75

Article number	55000.100.075
Brand	-
UBB	951351770791
UNSPSC	31161620
EAN	8715492320537
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	75 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	75
P	1.5
s	17

Technical Drawing

