

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M10X130

Article number	55000.100.130
Brand	-
UBB	950351849514
UNSPSC	31161620
EAN	8715492320599
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	130
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	17
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	32
b (min.): L>200mm	45
b (min.): L≤125mm	26
k	6.4
P	1.50
s	17

Technical Drawing

