

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M10X140

Article number	55000.100.140
Brand	-
UBB	950351849696
UNSPSC	31161620
EAN	8715492320605
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	140 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	140
P	1.5
s	17

Technical Drawing

