

Hexagon head bolt DIN 931 Stainless steel A4 70 M12X85

Article number	55000.120.085
Brand	-
UBB	500571367852
UNSPSC	31161620
EAN	8715494143905
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	85
Class	70
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	19
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm<L≤200mm	36
b (min.): L>200mm	49
b (min.): L≤125mm	30
k	7.5
P	1.75
s	19

Technical Drawing

