

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M12X300

Article number	55000.120.300
Brand	-
UBB	500571539138
UNSPSC	31161620
EAN	8715494120708
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	300
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	19
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mm<L≤200mm	36
b (min.): L>200mm	49
b (min.): L≤125mm	30
k	7.5
P	1.75
s	19

Technical Drawing

