

Hexagon head bolt DIN 931 Stainless steel A4 70 M14X50

Article number	55000.140.050
Brand	-
UBB	500633332514
UNSPSC	31161620
EAN	8715494616041
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	50 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	50
P	2
s	22

Technical Drawing

