

Hexagon head bolt DIN 931 Stainless steel A4 70 M14X60

Article number	55000.140.060
Brand	-
UBB	951351772102
UNSPSC	31161620
EAN	8715492320933
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	60 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
NEN	1555
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	60
P	2
s	22

Technical Drawing

