

Hexagon head bolt DIN 931 Stainless steel A4 70 M14X110

Article number	55000.140.110
Brand	-
UBB	951351772771
UNSPSC	31161620
EAN	8715492320988
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M14
Length (L) (mm)	110
Class	70
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	22
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mm<L≤200mm	40
b (min.): L>200mm	53
b (min.): L≤125mm	34
k	8.8
P	2
s	22

Technical Drawing

