

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M16X300

Article number	55000.160.300
Brand	-
UBB	951351774678
UNSPSC	31161620
EAN	8715492321282
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M16
Length	300 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	300
P	2
s	24

Technical Drawing

