

Hexagon head bolt DIN 931 Stainless steel A4 70 M18X65

Article number	55000.180.065
Brand	-
UBB	951351774751
UNSPSC	31161620
EAN	8715492321305
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	65 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	65
P	2.5
s	27

Technical Drawing

