

Hexagon head bolt DIN 931 Stainless steel A4 70 M18X140

Article number	55000.180.140
Brand	-
UBB	500571369346
UNSPSC	31161620
EAN	8715494144056
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M18
Length (L) (mm)	140
Class	70
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm<L≤200mm	48
b (min.): L>200mm	61
b (min.): L≤125mm	42
k	11.5
P	2.50
s	27

Technical Drawing

