

Hexagon head bolt DIN 931 Stainless steel A4 70 M20X100

Article number	55000.200.100
Brand	-
UBB	950351853136
UNSPSC	31161620
EAN	8715492321435
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	100 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	100
P	2.5
s	30

Technical Drawing

