

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M20X420

Article number	55000.200.420
Brand	-
UBB	500633335749
UNSPSC	31161620
EAN	8715494616362
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M20
Length	420 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	420
P	2.5
s	30

Technical Drawing

