

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M22X130

Article number	55000.220.130
Brand	-
UBB	951351777564
UNSPSC	31161620
EAN	8715492321640
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M22
Length	130 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	56
b (min.): L200mm	69
b (min.): L≤125mm	50
d-D	M22
k	14
L (mm)	130
P	2.5
s	32

Technical Drawing

