

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M24X160

Article number	55000.240.160
Brand	-
UBB	950351854878
UNSPSC	31161620
EAN	8715492321770
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	160 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	160
P	3
s	36

Technical Drawing

