

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M24X260

Article number	55000.240.260
Brand	-
UBB	952351936952
UNSPSC	31161620
EAN	8715492321855
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	260 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	260
P	3
s	36

Technical Drawing

