

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M24X280

Article number	55000.240.280
Brand	-
UBB	500571370989
UNSPSC	31161620
EAN	8715494144216
PKG. of 5	Full Box Only

Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	280
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm<L≤200mm	60
b (min.): L>200mm	73
b (min.): L≤125mm	54
k	15
P	3
s	36

Technical Drawing

