

## Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M27X120

Article number	55000.270.120
Brand	-
UBB	950351855370
UNSPSC	31161620
EAN	8715492321909
PKG. of 3	Full Box Only

### Technical Parameters

Diameter (d-D)	M27
Length (L) (mm)	120
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info  
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

### Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M

### Technical Specification

b (min.): 125mm<L≤200mm	66
b (min.): L>200mm	79
b (min.): L≤125mm	60
k	17
P	3
s	41

### Technical Drawing

