

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M27X130

Article number	55000.270.130
Brand	-
UBB	950351855453
UNSPSC	31161620
EAN	8715492321916
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	130 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	130
P	3
s	41

Technical Drawing

