

Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M27X250

Article number	55000.270.250
Brand	-
UBB	500571371631
UNSPSC	31161620
EAN	8715494138970
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M27
Length	250 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	250
P	3
s	41

Technical Drawing

