



**Hexagon socket button head screw with flange ISO 7380-2
Stainless steel A4 M3X3**

Article number	55025.030.003
Brand	-
UBB	500634448681
UNSPSC	31161518
EAN	8715494560610
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	3 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

ISO	7380-2
-----	--------

Technical Specification

d-D	M3
dc (max.)	6.9
Full thread if $L \leq$	20
k (max.)	1.65
L (mm)	3
P	0.5
s	2

Technical Drawing

