



Hexagon socket button head screw with flange ISO 7380-2 Stainless steel A4 M6X60

Article number	55025.060.060
Brand	-
UBB	500634455017
UNSPSC	31161518
EAN	8715494632997
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	60
Material	Stainless steel
Head shape	Button head
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

ISO	7380-2
-----	--------

d_c (max.)	13.6
Full thread if $L \leq$	30
k (max.)	3.3
P	1
s	4

