


Hexagon socket button head screw ISO 7380-1 Stainless steel A4 M12X50



Article number	55030.120.050
Brand	-
UBB	500633362628
UNSPSC	31161518
EAN	8715494619059
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	50
Material	Stainless steel
Head shape	Button head
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A4

Standards

NF	≈E25-126
ISO	7380-1
BS	≈4168-6
ASME	≈B18.3.4M

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

d_k (max.)	21
Full thread if $L \leq$	50
k (max.)	6.6
P	1.75
s	8

