



Hexalobular socket button head screw ISO ≈7380-1 Stainless steel A4 M3X8

Article number	55032.030.008
Brand	-
UBB	500634458243
UNSPSC	31161518
EAN	8715494554343
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Driving features	Hexalobular
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

NF	≈E25-126
ISO	≈7380-1
BS	≈4168-6
ASME	≈B18.3.4M

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Technical Specification

d-D	M3
dk (max.)	5.7
k (max.)	1.65
L (mm)	8
P	0.5
Socket	10

Technical Drawing

