



**Hexalobular socket button
head screw ISO ≈7380-1
Stainless steel A4 M4X8**

Article number	55032.040.008
Brand	-
UBB	500634458409
UNSPSC	31161518
EAN	8715494554404
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Driving features	Hexalobular
Head shape	Button head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

ASME	≈B18.3.4M
BS	≈4168-6
ISO	≈7380-1
NF	≈E25-126

Technical Specification

d-D	M4
dk (max.)	7.6
k (max.)	2.2
L (mm)	8
P	0.7
Socket	20

Technical Drawing

