



Hexagon socket head cap screw with low head DIN 7984 Stainless steel A4 M4X4

| | |
|----------------|---------------|
| Article number | 55040.040.004 |
| Brand | - |
| UBB | 500633363956 |
| UNSPSC | 31161605 |
| EAN | 8715494619189 |
| PKG. of 1000 | Full Box Only |

Technical Parameters

| | |
|--------------------|----------------------|
| Diameter | M4 |
| Length | 4 mm |
| Driving features | Hexagon socket |
| Head shape | Low cylindrical head |
| Material | Stainless steel |
| Material technical | A4 |
| Thread direction | Right |
| Thread | Metric thread |

| | |
|------|--|
| Info | Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'. |
|------|--|

Standards

| | |
|-----|------|
| DIN | 7984 |
|-----|------|

Technical Specification

| | |
|-------------------------|-----|
| b (min.) | 14 |
| d-D | M4 |
| dk | 7 |
| Full thread if $L \leq$ | 20 |
| k | 2.8 |
| L (mm) | 4 |
| P | 0.7 |
| s | 2.5 |

Technical Drawing

