



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A4 M5X55

Article number	55042.050.055
Brand	-
UBB	500633372296
UNSPSC	31161605
EAN	8715494620017
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	55 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

DIN	6912
-----	------

Technical Specification

b (min.): $L \leq 125\text{mm}$	16
d-D	M5
dh	2.5
dk	8.5
Full thread if $L \leq$	20
k	3.5
L (mm)	55
P	0.8
s	4

Technical Drawing

