



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M1,6X6

Article number	55050.016.006
Brand	-
UBB	500500314884
UNSPSC	31161605
EAN	8715494230346
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.6
Length	6 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NF	E25-125
ASME	B18.3.1M
BS	4168-1
NEN	1241
ISO	4762
DIN	912

Technical Specification

b	15
d-D	M1.6
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	1.6
L (mm)	6
P	0.35
s	1.5

Technical Drawing

