

Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M2,5X40



Article number	55050.025.040
Brand	-
UBB	500633376255
UNSPSC	31161605
EAN	8715494620413
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M2.5
Length (L) (mm)	40
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A4
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NF	E25-125
BS	4168-1
ISO	4762
DIN	912
ASME	B18.3.1M

Technical Specification

b	17
d_k (max.)	4.5
Full thread if $L \leq$	25
k (max.)	2.5
P	0.45
s	2

Technical Drawing

