



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M3X60

Article number	55050.030.060
Brand	-
UBB	500633376909
UNSPSC	31161605
EAN	8715494620482
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	60 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NF	E25-125
NEN	1241
BS	4168-1
DIN	912
ASME	B18.3.1M
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	60
P	0.5
s	2.5

Technical Drawing

