



Hexagon socket head cap screw DIN 912 Stainless steel A4 70 M12X50

Article number	55050.120.050
Brand	-
UBB	950351879628
UNSPSC	31161605
EAN	8715492328748
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1241
BS	4168-1
ASME	B18.3.1M
NF	E25-125
ISO	4762
DIN	912

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	12
L (mm)	50
P	1.75
s	10

Technical Drawing

