

Hexagon socket countersunk head screw ISO 10642 Stainless steel A4 M6X140



Article number	55060.060.140
Brand	-
UBB	500633389530
UNSPSC	31161518
EAN	8715494621748
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	140
Material	Stainless steel
Head shape	Countersunk head
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A4

Standards

DIN	≈7991
ISO	10642

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

or with the steel grade only, e.g. 'A2'.

FABORY

Technical Specification

b (min.)	24
d_k (max.)	12.16
Full thread if $L \leq$	35
k (max.)	3.72
P	1
s	4
α	90°

Technical Drawing

