



Hexagon socket countersunk head screw ISO 10642 Stainless steel A4 M6X140

Article number	55060.060.140
Brand	-
UBB	500633389530
UNSPSC	31161518
EAN	8715494621748
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	140 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread

Standards

ISO	10642
DIN	≈7991

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	24
d-D	M6
dk (max.)	12.16
Full thread if $L \leq$	35
k (max.)	3.72
L (mm)	140
P	1
s	4
α	90

Technical Drawing

