



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M2X10

Article number	55110.020.010
Brand	-
UBB	950353289214
UNSPSC	31161504
EAN	8715492333469
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
NEN	≈2370
DIN	963
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	10
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

