



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M2,5X16

Article number	55110.025.016
Brand	-
UBB	950353290105
UNSPSC	31161504
EAN	8715492333568
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	16 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
NEN	≈2370
ISO	≈2009
BS	≈4183
NF	≈E25-123

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
L (mm)	16
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

