



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M2,5X20

Article number	55110.025.020
Brand	-
UBB	950353290287
UNSPSC	31161504
EAN	8715492333582
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	20 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
ISO	≈2009
NEN	≈2370
DIN	963

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
L (mm)	20
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

