



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M2,5X25

Article number	55110.025.025
Brand	-
UBB	500571381382
UNSPSC	31161504
EAN	8715494134705
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	25 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
NF	≈E25-123
ASME	≈B18.6.7M
DIN	963
NEN	≈2370

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
L (mm)	25
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

