

Slotted countersunk head screw DIN 963 Stainless steel A4 70 M3X30



Article number	55110.030.030
Brand	-
UBB	950353291012
UNSPSC	31161504
EAN	8715492333674
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	30
Class	70
Material	Stainless steel
Head shape	Countersunk head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

ASME	≈B18.6.7M
ISO	≈2009
NF	≈E25-123
DIN	963
BS	≈4183

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50
t (min.)	0.6

Technical Drawing

