



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M4X45

Article number	55110.040.045
Brand	-
UBB	951353576634
UNSPSC	31161504
EAN	8715492333810
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	45 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	963
BS	≈4183
NF	≈E25-123
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	45
n	1
P	0.7
t (min.)	0.8

Technical Drawing

