

Slotted countersunk head screw DIN 963 Stainless steel A4 70 M5X6



Article number	55110.050.006
Brand	-
UBB	950353292341
UNSPSC	31161504
EAN	8715492333841
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	6
Class	70
Material	Stainless steel
Head shape	Countersunk head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

ASME	≈B18.6.7M
ISO	≈2009
BS	≈4183
DIN	963
NF	≈E25-123

Technical Specification

Thread length (min.)	25
d_k (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
n	1.2
P	0.80
t (min.)	1

Technical Drawing

