



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M5X30

Article number	55110.050.030
Brand	-
UBB	950353293091
UNSPSC	31161504
EAN	8715492333919
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	30
n	1.2
P	0.8
t (min.)	1

Technical Drawing

