



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M5X35

Article number	55110.050.035
Brand	-
UBB	950353293174
UNSPSC	31161504
EAN	8715492333926
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈2370
NF	≈E25-123
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2009
DIN	963

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	35
n	1.2
P	0.8
t (min.)	1

Technical Drawing

